

**Clamping yoke
BS 35II KLBUE HOLDER**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The electromagnetic compatibility (EMC) of electrical machines and installations has become a very important aspect. Weidmüller is facing up to this challenge with the KLBÜ shield connection terminals. These are available in different versions.

General ordering data

Type	BS 35II KLBUE HOLDER
Order No.	1723800000
Version	Clamping yoke, Set of fixings, Steel, 35 mm
GTIN (EAN)	4008190377038
Qty.	10 pc(s).

Clamping yoke BS 35II KLBUE HOLDER

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	35 mm	Net weight	38.5 g
Diameter	3 mm		

Temperatures

Operating temperature	Storage temperature
-----------------------	---------------------

Rated data IECEx/ATEX

Marking EN 60079-7	Ex e II
--------------------	---------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Version	Clamping bracket		

Dimensions

TS 35 offset	26.5 mm
--------------	---------

Material data

Material	Steel	Colour	Silver
----------	-------	--------	--------

System specifications

Product family	Clamping yoke	Mounting rail	TS 35
----------------	---------------	---------------	-------

Classifications

ETIM 3.0	EC001741	UNSPSC	30-21-18-11
eClass 5.1	27-14-11-45	eClass 6.2	27-14-92-14
eClass 7.1	27-18-92-34		

Approvals

Approvals	
ROHS	Conform