

Conductor markers VT SFX 9/24 MC NE BL V0

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



SlimFix X are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

- Halogen-free material
- Flammability rating V0
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

General ordering data

Type	VT SFX 9/24 MC NE BL V0
Order No.	1727740002
Version	Conductor markers, MultiCard, 24 x 15 mm, Wemid, Colour: Blue
GTIN (EAN)	4008190382421
Qty.	320 pc(s).

Conductor markers

VT SFX 9/24 MC NE BL V0

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	24 mm	Width	15 mm
Height	0.5 mm	Depth	0.5 mm
Net weight	0.473 g		

General data

Colour	Blue	Material	Wemid
Material colour according to resistance code	6	Operating temperature range, max.	120 °C
Operating temperature range, min.	-50 °C	Size of labelling field	23.9x9 mm
Type of printing	blank	UL 94 flammability rating	V-0

Conductor and cable markers

Conductor O.D., max.	40 mm	Conductor O.D., min.	7 mm
Conductor cross-section, max.	150 mm ²	Conductor cross-section, min.	16 mm ²
Halogen	No		

Classifications

ETIM 3.0	EC001530	UNSPSC	44-12-17-08
eClass 5.1	27-14-91-03	eClass 6.2	27-14-91-03
eClass 7.1	27-14-91-03		

Approvals

Approvals	
ROHS	Conform

Downloads

M-Print® PRO configuration file [mc_sfx_9_24_mcf.zip](#)