

**Conductor markers  
VT SF 6/21 NE WS V0**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm<sup>2</sup>
- Markers in proven MultiCard format

**General ordering data**

Type	VT SF 6/21 NE WS V0
Order No.	<a href="#">1730560001</a>
Version	Conductor markers, MultiCard, 21 x 8.4 mm, Polyamide 66, Colour: White
GTIN (EAN)	4008190954611
Qty.	160 pc(s).

## Conductor markers VT SF 6/21 NE WS V0

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technische Daten

### Dimensions and weights

Length	21 mm	Width	8.4 mm
Height	8.5 mm	Depth	8.4 mm
Net weight	0.641 g		

### General data

Colour	White	Material	Polyamide 66
Material colour according to resistance code	9	Operating temperature range, max.	120 °C
Operating temperature range, min.	-50 °C	Size of labelling field	21x8.4 mm
Type of printing	blank	UL 94 flammability rating	V-0

### Conductor and cable markers

Conductor O.D., max.	7.8 mm	Conductor O.D., min.	5.8 mm
Conductor cross-section, max.	16 mm <sup>2</sup>	Conductor cross-section, min.	10 mm <sup>2</sup>
Halogen	No		

### Classifications

ETIM 3.0	EC001530	UNSPSC	44-12-17-08
eClass 5.1	27-14-91-03	eClass 6.2	27-14-91-03
eClass 7.1	27-14-91-03		

### Approvals

Approvals	
ROHS	Conform

### Downloads

M-Print <sup>®</sup> PRO configuration file	<a href="#">mc_sf_6_21_mcf.zip</a>
---	------------------------------------