

**Cable markers
CLI M 2-4 WS/SW 9 MP**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



CLI M identification markers are slid onto CLI MH carrier strips and secured by means of cable ties. The system is particularly suitable for large conductor and cable cross-sections.

Advantages:

- Combination marker for cable and pipe markers
- One size for all diameters above 16 mm²
- Unrestricted combination options
- Closed, permanently attached markers
- Very good legibility

General ordering data

Type	CLI M 2-4 WS/SW 9 MP
Order No.	1733651530
Version	Cable markers, 4 x 11.3 mm, PVC, soft, without Cadmium, Colour: White
GTIN (EAN)	4032248451180
Qty.	100 pc(s).

Cable markers CLI M 2-4 WS/SW 9 MP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	4 mm	Width	11.3 mm
Height	3 mm	Depth	3 mm
Net weight	0.13 g		

General data

Colour	White	Colour of printing	Black
Material	PVC, soft, without Cadmium	Material colour according to resistance code	9
Operating temperature range, max.	80 °C	Operating temperature range, min.	-30 °C
Orientation of print	horizontal	Printed characters	Numbers
Printing	9	Printing method	Laser print
Recommended industries	Process, Machinery	Type of printing	Standard
UL 94 flammability rating	V-0		

Conductor and cable markers

Conductor O.D., max.	317 mm	Conductor O.D., min.	10 mm
Conductor cross-section, max.	500 mm ²	Conductor cross-section, min.	16 mm ²

Classifications

ETIM 3.0	EC001530	UNSPSC	44-12-17-08
eClass 5.1	27-14-91-03	eClass 6.2	27-14-91-29
eClass 7.1	27-14-91-29		

Approvals

Approvals	
ROHS	Conform

Cable markers CLI M 2-4 WS/SW 9 MP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen



Product is similar to illustration