


Cable markers
CLI M 2-4 GE/SW H MP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



{Reference (Object) not found: prod32188158582590}

General ordering data

Type	CLI M 2-4 GE/SW H MP
Order No.	1733651651
Version	Cable markers, 4 x 11.3 mm, PVC, soft, without Cadmium, Colour: Yellow
GTIN (EAN)	4008190398125
Qty.	100 pc(s).

Cable markers CLI M 2-4 GE/SW H MP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	4 mm	Width	11.3 mm
Height	3 mm	Depth	3 mm
Net weight	0.12 g		

General data

Colour	Yellow	Colour of printing	Black
Material	PVC, soft, without Cadmium	Material colour according to resistance code	4
Operating temperature range, max.	80 °C	Operating temperature range, min.	-30 °C
Orientation of print	horizontal	Printed characters	Upper-case letters
Printing	H	Printing method	Laser print
Recommended industries	Process, Machinery	Type of printing	Standard
UL 94 flammability rating	V-0		

Conductor and cable markers

Conductor O.D., max.	317 mm	Conductor O.D., min.	10 mm
Conductor cross-section, max.	500 mm ²	Conductor cross-section, min.	16 mm ²

Classifications

ETIM 3.0	EC001530	UNSPSC	44-12-17-08
eClass 5.1	27-14-91-03	eClass 6.2	27-14-91-29
eClass 7.1	27-14-91-29		

Approvals

Approvals	
ROHS	Conform

Cable markers CLI M 2-4 GE/SW H MP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen



Product is similar to illustration