

**Accessories
GWDR M40-NP**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The range of cable glands is rounded off by a large number of accessories.

General ordering data

Type	GWDR M40-NP
Order No.	1736270000
Version	Sealing ring, Neoprene, RAL 9005, External thread: M 40
GTIN (EAN)	4008190956066
Qty.	20 pc(s).

Accessories GWDR M40-NP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight	2 g
------------	-----

Width

Thickness	1.5 mm
-----------	--------

General information

Cable gland	metric	Colour code	RAL 9005
Diameter of sealing ring	52 mm	External thread	M 40
Inside diameter D2	40 mm	Material	Neoprene
O.D.	52 mm	Operating temperature range, max.	100 °C
Operating temperature range, min.	-30 °C	Pitch of thread	1.5 mm
Thickness	1.5 mm		

Classifications

ETIM 3.0	EC000781	UNSPSC	31-16-18-18
eClass 5.1	23-07-90-90	eClass 6.2	27-14-91-09
eClass 7.1	27-14-91-09		

Product information

Descriptive text ordering data	Further versions on request
--------------------------------	-----------------------------

Approvals

Approvals	
ROHS	Conform

Accessories GWDR M40-NP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

