

**SKMU MS (brass locknut)**  
**SKMU M40 MS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Weidmüller has a variety of different cable and wire entry systems in the Portfolio: with different designs of plastic, brass and stainless steel cable glands in the IP66, 67, 68 or IP69k protection classes. As a complete alternative to cable glands, pre-assembled cables with modular multi-wire or multi-cable entry systems can be simply and quickly inserted into electrical equipment. Last but not least, Weidmüller offers EX-certified cable glands and cable/wire entry systems.

- Cable glands made from plastic and brass
- EMC screwed joints
- for areas at risk of explosion
- VDE, CSA and UL approvals

**General ordering data**

|            |                                                                      |
|------------|----------------------------------------------------------------------|
| Type       | SKMU M40 MS                                                          |
| Order No.  | <a href="#">1737030000</a>                                           |
| Version    | SKMU MS (brass locknut), Locknut, M 40, 4.5 mm, Brass, nickel-plated |
| GTIN (EAN) | 4008190956509                                                        |
| Qty.       | 50 pc(s).                                                            |

**SKMU MS (brass locknut)**  
**SKMU M40 MS**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

Net weight 4.92 g

**Environmental Product Compliance**

REACH SVHC Lead 7439-92-1

**Width**

Thickness 4 mm

**General information**

|                  |         |                 |                      |
|------------------|---------|-----------------|----------------------|
| AF size 1        | 44 mm   | Cable glands    | metric               |
| External thread  | M 40    | Internal thread | M 40                 |
| Length of thread | 4.5 mm  | Material        | Brass, nickel-plated |
| O.D.             | 50.8 mm | Pitch of thread | 1.5 mm               |
| Thickness        | 4 mm    |                 |                      |

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000940    | ETIM 4.0   | EC000441    |
| ETIM 5.0   | EC000441    | ETIM 6.0   | EC000940    |
| UNSPSC     | 30-21-18-01 | eClass 5.1 | 23-11-07-01 |
| eClass 6.2 | 27-14-91-09 | eClass 7.1 | 27-14-91-09 |
| eClass 8.1 | 27-14-91-09 | eClass 9.0 | 27-14-44-24 |
| eClass 9.1 | 27-14-44-24 |            |             |

**Approvals**

ROHS Conform

**Downloads**

|                    |                                     |
|--------------------|-------------------------------------|
| Brochure/Catalogue | <a href="#">CAT 5 ENCL 17/18 EN</a> |
| Engineering Data   | <a href="#">EPLAN.WSCAD</a>         |
| Engineering Data   | <a href="#">STEP</a>                |

**Data sheet****SKMU MS (brass locknut)  
SKMU M40 MS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**