

Conductor markers SFC 1/12 MC NE GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The SlimFix Clip combines two advantages: its unique closure mechanism offers the reliability of a closed marker with the ease of installation of an open marker. The clip mechanism allows quick and convenient installation of the marker even after the conductor has been installed. SlimFix Clips are suitable for conductors and cables with an outside diameter of up to 5 mm. The large marking surface - up to 30 mm - enables long character strings. The material is halogen-free and complies with flammability rating V2.

- Halogen-free material
- Flammability rating V2
- Fast installation without tools
- Markers in proven MultiCard format
- Available in the lengths of 12 mm, 21 mm and 30 mm

General ordering data

Type	SFC 1/12 MC NE GE
Order No.	1747320004
Version	Conductor markers, MultiCard, 12 x 5.8 mm, Polyamide 66, Colour: Yellow
GTIN (EAN)	4008190995508
Qty.	200 pc(s).

Conductor markers SFC 1/12 MC NE GE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	12 mm	Width	5.8 mm
Height	7 mm	Depth	5 mm
Net weight	0.49 g		

General data

Colour	Yellow	Material	Polyamide 66
Material colour according to resistance code	4	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Recommended industries	Machinery
Size of labelling field	12x4.1 mm	Type of printing	blank
UL 94 flammability rating	V-2		

Conductor and cable markers

Conductor O.D., max.	3.5 mm	Conductor O.D., min.	2 mm
Conductor cross-section, max.	2.5 mm ²	Conductor cross-section, min.	0.75 mm ²
Halogen	No		

Classifications

ETIM 3.0	EC001530	UNSPSC	44-12-17-08
eClass 5.1	27-14-91-03	eClass 6.2	27-14-91-03
eClass 7.1	27-14-91-03		

Approvals

Approvals	
ROHS	Conform

Downloads

M-Print® PRO configuration file	mc_sfc_1_12_mcf.zip
---------------------------------	-------------------------------------