

**Clamping yoke  
KLBUE CO 4**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)



The electromagnetic compatibility (EMC) of electrical machines and installations has become a very important aspect. Weidmüller is facing up to this challenge with the KLBÜ shield connection terminals. These are available in different versions.

**General ordering data**

|            |                                            |
|------------|--------------------------------------------|
| Type       | KLBUE CO 4                                 |
| Order No.  | <a href="#">1749161001</a>                 |
| Version    | Clamping yoke, Clamping yoke, Steel, 32 mm |
| GTIN (EAN) | 4032248064458                              |
| Qty.       | 10 pc(s).                                  |

## Clamping yoke KLBUE CO 4

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technische Daten

### Dimensions and weights

|        |       |            |          |
|--------|-------|------------|----------|
| Length | 32 mm | Width      | 25 mm    |
| Height | 56 mm | Net weight | 53.252 g |

### Temperatures

|                       |                     |
|-----------------------|---------------------|
| Operating temperature | Storage temperature |
|-----------------------|---------------------|

### Additional technical data

|                          |                         |                     |        |
|--------------------------|-------------------------|---------------------|--------|
| Explosion-tested version | No                      | Installation advice | Busbar |
| Version                  | For a shield connection |                     |        |

### Wire clamp for cable diameter

|                      |       |                      |       |
|----------------------|-------|----------------------|-------|
| Cable diameter, min. | 15 mm | Cable diameter, max. | 28 mm |
|----------------------|-------|----------------------|-------|

### Material data

|          |       |
|----------|-------|
| Material | Steel |
|----------|-------|

### System specifications

|                |               |
|----------------|---------------|
| Product family | Clamping yoke |
|----------------|---------------|

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000489    | UNSPSC     | 30-21-18-01 |
| eClass 6.2 | 27-14-11-90 | eClass 7.1 | 27-14-11-50 |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|