

**Clamping yoke
KLBUE 4-13.5 CPF**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The electromagnetic compatibility (EMC) of electrical machines and installations has become a very important aspect. Weidmüller is facing up to this challenge with the KLBÜ shield connection terminals. These are available in different versions.

General ordering data

Type	KLBUE 4-13.5 CPF
Order No.	1752691001
Version	Clamping yoke, Clamping yoke, Steel, 22 mm
GTIN (EAN)	4032248044429
Qty.	10 pc(s).

Clamping yoke KLBUE 4-13.5 CPF

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	22 mm	Width	20.5 mm
Height	31.5 mm	Height of lowest version	44 mm
Net weight	23.1 g		

Temperatures

Operating temperature	Storage temperature
-----------------------	---------------------

Rated data IECEx/ATEX

Marking EN 60079-7	Ex e II	Marking ATEX Directive 94/9/EC	II 2 G D
--------------------	---------	--------------------------------	----------

Additional technical data

Explosion-tested version	No	Version	For a shield connection
--------------------------	----	---------	-------------------------

Wire clamp for cable diameter

Cable diameter, min.	4 mm	Cable diameter, max.	13.5 mm
----------------------	------	----------------------	---------

Material data

Material	Steel	Colour	Grey
----------	-------	--------	------

System specifications

Product family	Clamping yoke
----------------	---------------

Classifications

ETIM 3.0	EC000489	UNSPSC	30-21-18-01
eClass 6.2	27-14-11-90	eClass 7.1	27-14-11-50

Approvals

ROHS	Conform
------	---------