

**Clamping yoke
KLBUE CO 5**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The electromagnetic compatibility (EMC) of electrical machines and installations has become a very important aspect. Weidmüller is facing up to this challenge with the KLBÜ shield connection terminals.

These are available in different versions.

General ordering data

Type	KLBUE CO 5
Order No.	1755081001
Version	Clamping yoke, Clamping yoke, Steel, 35.5 mm
GTIN (EAN)	4032248064472
Qty.	10 pc(s).

Clamping yoke KLBUE CO 5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	35.5 mm	Width	42.7 mm
Height	64.5 mm	Net weight	78.7 g

Temperatures

Operating temperature	Storage temperature
-----------------------	---------------------

Additional technical data

Explosion-tested version	No	Installation advice	Busbar
Version	For a shield connection		

Wire clamp for cable diameter

Cable diameter, min.	20 mm	Cable diameter, max.	37 mm
----------------------	-------	----------------------	-------

Material data

Material	Steel
----------	-------

System specifications

Product family	Clamping yoke
----------------	---------------

Classifications

ETIM 3.0	EC000489	UNSPSC	30-21-18-01
eClass 6.2	27-14-11-90	eClass 7.1	27-14-11-50

Approvals

ROHS	Conform
------	---------