

**Conductor markers
CLI T 1-20**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The CLI T sleeve is a high-quality, transparent sleeve for marking conductors and cables with cross-sections up to 75 mm². The CLI T sleeve is available in four lengths so that labelling with long character strings is possible. The transparent sleeve optimally protects the inlay tag against outside influences. The CLI F or TM-I inlay tags are used with this sleeve.

- Wider cross-section range per sleeve
- A special flexible bellow profile ensures a wide application range
- Easy insertion of the TM-I tag into the sleeve pocket before or after connecting the conductor
- Available in five lengths
- Not suitable for labelling with P-Ink or STI pen

General ordering data

Type	CLI T 1-20
Order No.	1764220000
Version	Conductor markers, 20 x 5 mm, PVC, Colour: Transparent, Conductor O.D.:
GTIN (EAN)	4032248053285
Qty.	200 pc(s).

**Conductor markers
CLI T 1-20**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten**Dimensions and weights**

Length	20 mm	Width	5 mm
Height	8 mm	Depth	8 mm
Net weight	0.352 g		

General data

Colour	Transparent	Material	PVC
Operating temperature range, max.	80 °C	Operating temperature range, min.	-30 °C
Recommended industries	Transportation, Machinery	Type of printing	blank
UL 94 flammability rating	V-0		

Conductor and cable markers

Conductor O.D., max.	5 mm	Conductor O.D., min.	2.5 mm
Conductor cross-section, max.	6 mm ²	Conductor cross-section, min.	0.75 mm ²
Halogen	Yes		

Classifications

ETIM 3.0	EC001530	UNSPSC	44-12-17-08
eClass 5.1	27-14-91-03	eClass 6.2	27-14-91-29
eClass 7.1	27-14-91-29		

Approvals

ROHS	Conform
------	---------