

Z-series
ZAD 1/4-2 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Weidmüller offers users of modular terminals of the Z-Series a comprehensive range of accessories that render possible appropriate solutions for all - even non-standard - tasks.

The accessories must comply with the same quality standards as the modular terminals themselves.

General ordering data

Type	ZAD 1/4-2 GE
Order No.	1764560000
Version	Z-series, Cover
GTIN (EAN)	4032248066063
Qty.	20 pc(s).

Datenblatt

Z-series ZAD 1/4-2 GE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	20.4 mm	Width	8 mm
Height	10.15 mm	Net weight	0.4 g

Temperatures

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Version	pluggable		

Clampable wires (rated connection)

Type of connection	Tension clamp connection	Connection direction	top
--------------------	--------------------------	----------------------	-----

Material data

Material	Wemid	Colour	Yellow
UL 94 flammability rating	V-0		

System specifications

Product family	Z-series	Type of connection	Tension clamp connection
Connection direction	top	End cover plate required	Yes

Classifications

ETIM 3.0	EC000886	UNSPSC	30-21-18-27
eClass 5.1	27-14-11-33	eClass 6.2	27-14-11-33
eClass 7.1	27-14-11-33		

Approvals

Approvals	
ROHS	Conform