

**Accessories  
ZF 4 S BL**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



The accessories of the other ranges of modular terminals can also be used for the P-Series in order to reduce the number of variations. The accessories render possible appropriate solutions for all - even non-standard - tasks. The accessories must comply with the same quality standards as the modular terminals themselves.

**General ordering data**

Type	ZF 4 S BL
Order No.	<a href="#">1814660000</a>
Version	Accessories, Special terminal, Rated cross-section: 2.5 mm <sup>2</sup> , Tension clamp connection, Wemid, Blue, Busbar
GTIN (EAN)	4032248302956
Qty.	50 pc(s).

**Accessories  
ZF 4 S BL**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technische Daten**

**Dimensions and weights**

Length	24.5 mm	Width	6.1 mm
Height	22 mm	Net weight	4.58 g

**Temperatures**

Operating temperature	Storage temperature
-----------------------	---------------------

**Additional technical data**

Installation advice	Busbar	Version	15 x 6 mm busbar connection
---------------------	--------	---------	-----------------------------

**Clampable wires (rated connection)**

Type of connection	Tension clamp connection	Stripping length	10 mm
Connection direction	on side	Number of connections	1
Wire connection cross section, solid core, max. rated connection	0.5 mm <sup>2</sup>	Wire connection cross section, solid core max. rated connection	4 mm <sup>2</sup>
Wire connection cross section, finely stranded, max.	2.5 mm <sup>2</sup>	Wire connection cross-section, finely stranded, min.	0.5 mm <sup>2</sup>

**Rated data**

Rated cross-section	2.5 mm <sup>2</sup>	Rated voltage	400 V
Rated impulse withstand voltage	6 kV	Rated current	24 A
Standards	IEC 60947-7-1	Pollution severity	3
Surge voltage category	III		

**Material data**

Insulating material	Wemid	Material	Wemid
Colour	Silver	UL 94 flammability rating	V-0

**System specifications**

Product family	Accessories	Type of connection	Tension clamp connection
Connection direction	on side	Number of connections	1

**Classifications**

ETIM 3.0	EC000001	UNSPSC	30-21-18-11
eClass 5.1	27-14-11-31	eClass 6.2	27-14-11-90
eClass 7.1	27-14-11-90		

**Approvals**

Approvals



ROHS Conform