

W-Series, Accessories
WQV 50N/2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The versatile and extensive range of products - from 0.05 mm² to 300 mm² - means that you have diverse options for your applications at your disposal.
Hardened steel for mechanical strength and high-quality tinned copper for optimum conductivity. All materials comply with RoHS requirements and have been tested to current environment guidelines.

General ordering data

Type	WQV 50N/2
Order No.	1834060000
Version	W-Series, Accessories, Cross-connector, For the terminals, No. of poles: 2
GTIN (EAN)	4032248379859
Qty.	5 pc(s).

W-Series, Accessories WQV 50N/2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	28.5 mm	Width	9.5 mm
Height	17.5 mm	Net weight	21.78 g

Temperatures

Operating temperature	Storage temperature
-----------------------	---------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Version	For the terminals		

Rated data

Rated current	150 A
---------------	-------

Material data

Material	Steel	Colour	Grey
----------	-------	--------	------

System specifications

Product family	W-Series, Accessories
----------------	-----------------------

Classifications

ETIM 3.0	EC000489	UNSPSC	30-21-18-01
eClass 5.1	27-14-11-40	eClass 6.2	27-14-11-40
eClass 7.1	27-14-11-40		

Approvals

ROHS	Conform
------	---------

Downloads

STEP	1834060000_33979_WQV-50N-2_STP.stp
3D Modell	