

**Clamping yoke
KLBUE 3-8 SDSC**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The electromagnetic compatibility (EMC) of electrical machines and installations has become a very important aspect. Weidmüller is facing up to this challenge with the KLBÜ shield connection terminals.

These are available in different versions.

General ordering data

Type	KLBUE 3-8 SDSC
Order No.	1835840000
Version	Clamping yoke, Clamping yoke, Steel, 18 mm
GTIN (EAN)	4032248394555
Qty.	10 pc(s).

Clamping yoke KLBUE 3-8 SDSC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	18 mm	Width	14.4 mm
Height	25.9 mm	Net weight	12.6 g

Temperatures

Operating temperature	Storage temperature
-----------------------	---------------------

Additional technical data

Installation advice	Direct mounting, Busbar	Version	For a shield connection
---------------------	-------------------------	---------	-------------------------

Wire clamp for cable diameter

Cable diameter, min.	3 mm	Cable diameter, max.	8 mm
----------------------	------	----------------------	------

Material data

Material	Steel
----------	-------

System specifications

Product family	Clamping yoke
----------------	---------------

Classifications

ETIM 3.0	EC000489	eClass 6.2	27-14-11-90
eClass 7.1	27-14-11-50		

Product information

Descriptive text technical data	Clamping bracket length including self-tapping screw.
---------------------------------	---

Approvals

Approvals	
ROHS	Conform