

**Z-series
FEKO ZRV2.5 0.2-0.35****Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

One terminal strip for the functional unit, one plug-in connector for the cable loom fabrication. All that remains to be done is to clip the two units together during final assembly – just like a plug-in connector. Finished! Whether for railway engineering, mechanical engineering or shipbuilding applications, all are served excellently by the products of the Weidmüller Z-Series. This is because the products are easy to use and practical, and the connections are simple, reliable and quick. Modular and flexible connection systems are especially in demand where complete functional units have to be prefabricated or replaced.

General ordering data

Type	FEKO ZRV2.5 0.2-0.35
Order No.	1854750000
Version	Z-series, Multi-tier modular terminal, 4.15 mm, Grey, Direct mounting
GTIN (EAN)	4032248401321
Qty.	5,000 pc(s).

Z-series FEKO ZRV2.5 0.2-0.35

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	19.8 mm	Width	4.15 mm
Height	3.1 mm	Net weight	0.612 g

Temperatures

Operating temperature	Storage temperature
-----------------------	---------------------

Additional technical data

Installation advice	Direct mounting	Version	Spring contact
---------------------	-----------------	---------	----------------

Clampable wires (rated connection)

Type of connection	Spring contact
--------------------	----------------

Rated data

Rated cross-section	2.5 mm ²
---------------------	---------------------

Material data

Colour	Grey
--------	------

System specifications

Product family	Z-series	Type of connection	Spring contact
----------------	----------	--------------------	----------------

Classifications

ETIM 3.0	EC000897	UNSPSC	30-21-18-11
eClass 5.1	27-14-11-18	eClass 6.2	27-14-91-37
eClass 7.1	27-14-91-37		

Approvals

Approvals	
ROHS	Conform