


**Z-series, WeiCoS
ZT 4/2AN/1**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



One terminal strip for the functional unit, one plug-in connector for the cable loom fabrication. All that remains to be done is to clip the two units together during final assembly – just like a plug-in connector. Finished! Whether for railway engineering, mechanical engineering or shipbuilding applications, all are served excellently by the products of the Weidmüller Z-Series. This is because the products are easy to use and practical, and the connections are simple, reliable and quick. Modular and flexible connection systems are especially in demand where complete functional units have to be prefabricated or replaced.

General ordering data

Type	ZT 4/2AN/1
Order No.	1854960000
Version	Z-series, WeiCoS, Feed-through terminal, Rated cross-section: 4 mm ² , Tension clamp connection, Wemid, Dark Beige
GTIN (EAN)	4032248395705
Qty.	50 pc(s).

**Z-series, WeiCoS
ZT 4/2AN/1**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten
Dimensions and weights

Length	58 mm	Width	6.5 mm
Height	43 mm	Height of lowest version	43.5 mm
Net weight	11.18 g		

Temperatures

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

Additional technical data

Explosion-tested version	No	Open sides	right
Type of mounting		Version	2 tension-clamp connections - 1 plug-in connection, pluggable
	Snap-on		

CSA ratings data

Certificate No. (CSA)	200039-1720292	Voltage size C (CSA)	600 V
Current size C (CSA)	28 A	Wire cross section max. (CSA)	10 AWG
Wire cross section min. (CSA)	26 AWG		

Clampable wires (additional connection)

Conductor cross-section, flexible plus plastic collar DIN 46228/1, further connection, min.	0.5 mm ²	Conductor cross-section, flexible plus plastic collar DIN 46228/1, further connection, max.	4 mm ²
---	---------------------	---	-------------------

Clampable wires (rated connection)

Type of connection	Tension clamp connection	Type of connection 2	Plug-in connection
Stripping length	12 mm	Blade size	0.6 x 3.5 mm
Connection direction	top	Number of connections	1
Clamping range, rated connection, min.	0.13 mm ²	Clamping range, rated connection, max.	6 mm ²
Gauge to IEC 60947-1	A3	Wire connection cross section, solid core, max. rated connection	0.5 mm ²
Wire connection cross section, solid core max. rated connection	6 mm ²	Wire connection cross section, finely stranded, max.	6 mm ²
Wire connection cross-section, finely stranded, min.	0.5 mm ²	Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, min.	0.5 mm ²
Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, max.	4 mm ²	Wire connection cross section AWG, min.	AWG 26
Wire connection cross section AWG, max.	AWG 10		

Rated data

Rated cross-section	4 mm ²	Rated voltage	800 V
Rated impulse withstand voltage	8 kV	Rated current	32 A
Current at maximum wires	32 A	Standards	IEC 60947-7-1, IEC 61984
Pollution severity	3	Max. voltage of clamp support & pluggable system	800 V

Z-series, WeiCoS ZT 4/2AN/1

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

UL ratings data

Certificate No. (cURus)	E60693	Conductor size Factory wiring max. (cURus)	10 AWG
Conductor size Factory wiring min. (cURus)	26 AWG	Conductor size Field wiring max. (cURus)	10 AWG
Conductor size Field wiring min. (cURus)	26 AWG	Current size C (cURus)	28 A
Voltage size C (cURus)	600 V		

Material data

Insulating material	Wemid	Material	Wemid
Colour	Dark Beige	UL 94 flammability rating	V-0

System specifications

Product family	Z-series, WeiCoS	Type of connection	Tension clamp connection
Type of connection 2	Plug-in connection	Connection direction	top
Number of levels	1	Number of connections	1
No. of clamping points per level	1	Levels cross-connected internally	No
Mounting rail	TS 35	End cover plate required	Yes

Classifications

ETIM 3.0	EC000897	UNSPSC	30-21-18-11
eClass 5.1	27-14-11-20	eClass 6.2	27-14-92-14
eClass 7.1	27-14-92-14		

Product information

Descriptive text technical data	CSA current and voltage, acc. to Gr. C
---------------------------------	--

Approvals

Approvals



ROHS	Conform
------	---------