

Q WDU10-4 SET**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The versatile and extensive range of products - from 0.05 mm² to 300 mm² - means that you have diverse options for your applications at your disposal.

Hardened steel for mechanical strength and high-quality tinned copper for optimum conductivity. All materials comply with RoHS requirements and have been tested to current environment guidelines.

General ordering data

Type	Q WDU10-4 SET
Order No.	1859610000
Version	Cross-connector
GTIN (EAN)	4032248413324
Qty.	10 pc(s).

Q WDU10-4 SET

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight	7.2 g
------------	-------

Additional technical data

Explosion-tested version	No	Installation advice	Feed-through (bushing), Direct mounting
--------------------------	----	---------------------	--

Rated data

Rated voltage	0 V
---------------	-----

Classifications

ETIM 3.0	EC000489	UNSPSC	30-21-18-01
eClass 5.1	27-14-11-40	eClass 6.2	27-14-11-40
eClass 7.1	27-14-11-40		

Approvals

Approvals	
ROHS	Conform