

W-Series, Accessories
Q WDU10-2.5 SET

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The versatile and extensive range of products - from 0.05 mm² to 300 mm² - means that you have diverse options for your applications at your disposal.
Hardened steel for mechanical strength and high-quality tinned copper for optimum conductivity. All materials comply with RoHS requirements and have been tested to current environment guidelines.

General ordering data

Type	Q WDU10-2.5 SET
Order No.	1859620000
Version	W-Series, Accessories, Cross-connector, For the terminals, No. of poles: 2
GTIN (EAN)	4032248413331
Qty.	10 pc(s).

W-Series, Accessories Q WDU10-2.5 SET

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	13.9 mm	Width	6 mm
Height	22.5 mm	Net weight	6.4 g

Temperatures

Operating temperature	Storage temperature
-----------------------	---------------------

Additional technical data

Explosion-tested version	No	Installation advice	Feed-through (bushing), Direct mounting
Version	For the terminals		

Material data

Material	Steel	Colour	Grey
----------	-------	--------	------

System specifications

Product family	W-Series, Accessories
----------------	-----------------------

Classifications

ETIM 3.0	EC000489	UNSPSC	30-21-18-01
eClass 5.1	27-14-11-40	eClass 6.2	27-14-11-40
eClass 7.1	27-14-11-40		

Approvals

Approvals	
ROHS	Conform