

W-Series, Accessories
WAP WSI4/2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The versatile and extensive range of products - from 0.05 mm² to 300 mm² - means that you have diverse options for your applications at your disposal.

Hardened steel for mechanical strength and high-quality tinned copper for optimum conductivity. All materials comply with RoHS requirements and have been tested to current environment guidelines.

General ordering data

Type	WAP WSI4/2
Order No.	1880450000
Version	W-Series, Accessories, End plate
GTIN (EAN)	4032248541911
Qty.	50 pc(s).

W-Series, Accessories WAP WSI4/2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Dimensions and weights

Length	71.12 mm	Width	2.5 mm
Height	49.49 mm	Net weight	6.56 g

Temperatures

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

Additional technical data

Installation advice	Feed-through (bushing)	Version	End plate
---------------------	------------------------	---------	-----------

Dimensions

TS 32 offset	36 mm	TS 35 offset	36 mm
--------------	-------	--------------	-------

Material data

Material	Wemid	Colour	Black
UL 94 flammability rating	V-0		

System specifications

Product family	W-Series, Accessories	Mounting rail	TS 35, TS 32
----------------	-----------------------	---------------	--------------

Classifications

ETIM 3.0	EC000886	UNSPSC	30-21-18-27
eClass 5.1	27-14-11-33	eClass 6.2	27-14-11-33
eClass 7.1	27-14-11-33		

Approvals

ROHS	Conform
------	---------