

## Device markers LM MT300 15X9 GE

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)



- Adhesive polyester labels
- Suitable for A4 laser printers
- Abrasion-resistant
- High heat resistance
- For marking all kinds of switchgear and modules
- Can also be written on with a ballpoint pen or STI marking pen

### General ordering data

|            |                                                                       |
|------------|-----------------------------------------------------------------------|
| Type       | LM MT300 15X9 GE                                                      |
| Order No.  | <a href="#">1882890000</a>                                            |
| Version    | Device markers, Label, 15 x 9 mm, Polyester, PVC-free, Colour: Yellow |
| GTIN (EAN) | 4032248486984                                                         |
| Qty.       | 10 pc(s).                                                             |

## Device markers LM MT300 15X9 GE

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |       |       |      |
|------------|-------|-------|------|
| Length     | 15 mm | Width | 9 mm |
| Net weight | 6.8 g |       |      |

### General data

|                                   |                     |                                              |             |
|-----------------------------------|---------------------|----------------------------------------------|-------------|
| Adhesive                          | Acrylate adhesive   | Colour                                       | Yellow      |
| Material                          | Polyester, PVC-free | Material colour according to resistance code | 4           |
| Number per sheet                  | 186                 | Operating temperature range, max.            | 150 °C      |
| Operating temperature range, min. | -40 °C              | Printing method                              | Laser print |
| UL 94 flammability rating         | HB                  | UL 969 flammability rating                   | Yes         |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001288    | UNSPSC     | 30-21-18-01 |
| eClass 5.1 | 27-14-91-29 | eClass 6.2 | 27-14-91-29 |
| eClass 7.1 | 27-14-91-29 |            |             |

### Approvals

|           |         |
|-----------|---------|
| Approvals |         |
| ROHS      | Conform |

### Downloads

|                                 |                                           |
|---------------------------------|-------------------------------------------|
| M-Print® PRO configuration file | <a href="#">lab_lm_mt300_15x9_mcf.zip</a> |
|---------------------------------|-------------------------------------------|