

## Device markers LM MT300 202x12 GE

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)



- Adhesive polyester labels
- Suitable for A4 laser printers
- Abrasion-resistant
- High heat resistance
- For marking all kinds of switchgear and modules
- Can also be written on with a ballpoint pen or STI marking pen

### General ordering data

|            |                                                                         |
|------------|-------------------------------------------------------------------------|
| Type       | LM MT300 202x12 GE                                                      |
| Order No.  | <a href="#">1915320000</a>                                              |
| Version    | Device markers, Label, 202 x 12 mm, Polyester, PVC-free, Colour: Yellow |
| GTIN (EAN) | 4032248547968                                                           |
| Qty.       | 10 pc(s).                                                               |

**Device markers  
LM MT300 202x12 GE**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technische Daten****Dimensions and weights**

|            |        |       |       |
|------------|--------|-------|-------|
| Length     | 202 mm | Width | 12 mm |
| Net weight | 13.8 g |       |       |

**General data**

|                                   |                     |                                              |             |
|-----------------------------------|---------------------|----------------------------------------------|-------------|
| Adhesive                          | Acrylate adhesive   | Colour                                       | Yellow      |
| Material                          | Polyester, PVC-free | Material colour according to resistance code | 4           |
| Number per sheet                  | 22                  | Operating temperature range, max.            | 150 °C      |
| Operating temperature range, min. | -40 °C              | Printing method                              | Laser print |
| UL 94 flammability rating         | HB                  | UL 969 flammability rating                   | Yes         |

**Classifications**

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001288    | UNSPSC     | 30-21-18-01 |
| eClass 5.1 | 27-14-91-29 | eClass 6.2 | 27-14-91-29 |
| eClass 7.1 | 27-14-91-29 |            |             |

**Approvals**

|           |         |
|-----------|---------|
| Approvals |         |
| ROHS      | Conform |

**Downloads**

|                                 |                                             |
|---------------------------------|---------------------------------------------|
| M-Print® PRO configuration file | <a href="#">lab_lm_mt300_202x12_mcf.zip</a> |
|---------------------------------|---------------------------------------------|