

**Conductor markers
SF 5/21 MC NE BL V2****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

General ordering data

Type	SF 5/21 MC NE BL V2
Order No.	1919150000
Version	Conductor markers, MultiCard, 21 x 7.4 mm, Polyamide 66, Colour: Blue
GTIN (EAN)	4032248555475
Qty.	160 pc(s).

**Conductor markers
SF 5/21 MC NE BL V2**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten**Dimensions and weights**

Length	21 mm	Width	7.4 mm
Height	8 mm	Net weight	0.975 g

General data

Colour	Blue	Material	Polyamide 66
Material colour according to resistance code	6	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Size of labelling field	21x7.4 mm
Type of printing	blank	UL 94 flammability rating	V-2

Conductor and cable markers

Conductor O.D., max.	7.4 mm	Conductor O.D., min.	4.8 mm
Conductor cross-section, max.	10 mm ²	Conductor cross-section, min.	6 mm ²
Halogen	No		

Classifications

ETIM 3.0	EC001530	UNSPSC	44-12-17-08
eClass 5.1	27-14-91-03	eClass 6.2	27-14-91-03
eClass 7.1	27-14-91-03		

Approvals

Approvals	
ROHS	Conform

Downloads

M-Print® PRO configuration file	mc_sf_5_21_mcf.zip
---------------------------------	------------------------------------