

W-Series, Accessories
WQS 2/16/5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The versatile and extensive range of products - from 0.05 mm² to 300 mm² - means that you have diverse options for your applications at your disposal.

Hardened steel for mechanical strength and high-quality tinned copper for optimum conductivity. All materials comply with RoHS requirements and have been tested to current environment guidelines.

General ordering data

Type	WQS 2/16/5
Order No.	1925070000
Version	W-Series, Accessories, Short-circuit plug, No. of poles:
GTIN (EAN)	4032248566174
Qty.	10 pc(s).

W-Series, Accessories
WQS 2/16/5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten**Dimensions and weights**

Length	24 mm	Width	11 mm
Height	36 mm	Net weight	18.7 g

Temperatures

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

Additional technical data

Installation advice	Direct mounting
---------------------	-----------------

Material data

Material	Wemid	Colour	Yellow
UL 94 flammability rating	V-0		

System specifications

Product family	W-Series, Accessories
----------------	-----------------------

Classifications

ETIM 3.0	EC000489	UNSPSC	30-21-18-01
eClass 5.1	27-14-11-40	eClass 6.2	27-14-11-40
eClass 7.1	27-14-11-40		

Approvals

ROHS	Conform
------	---------