

**Industrial Ethernet
IE-PH-RJ45-TH-GY****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Similar to illustration

Weidmüller IP 20 plug-in connectors in the crimp version are best used together with the antikink grommets available in various colours to help identify the plugs as well as protect locking levers and prevent strain on the cables.

Features:

- 7 different colours

General ordering data

Type	IE-PH-RJ45-TH-GY
Order No.	1962440000
Version	Bending protection sleeve, grey
GTIN (EAN)	4032248644476
Qty.	10 pc(s).

Industrial Ethernet IE-PH-RJ45-TH-GY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Net weight 2.4 g

Temperatures

Operating temperature

Classifications

ETIM 3.0	EC001121	ETIM 4.0	EC001121
ETIM 5.0	EC001121	ETIM 6.0	EC001679
UNSPSC	30-21-18-10	eClass 5.1	27-26-07-08
eClass 6.2	27-25-05-04	eClass 7.1	27-25-05-04
eClass 8.1	19-17-01-25	eClass 9.0	27-06-04-12
eClass 9.1	27-06-04-12		

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 9 IETH 15/16 EN MB FREECONTACT EN FL FIELDWIRING EN PI PROFINET CABLING EN
Engineering Data	EPLAN
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN