

W-Series
BFEL + BEMU WEW WTL 35

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Current and voltage transformer wiring**

Our test disconnect terminal blocks featuring spring and screw connection technology allow you to create all the important converter circuits for measuring current, voltage and power in a safe and sophisticated way.

General ordering data

Type	BFEL + BEMU WEW WTL 35
Order No.	1964820000
Version	W-Series, Fastening element
GTIN (EAN)	4032248651467
Qty.	20 pc(s).

W-Series
BFEL + BEMU WEW WTL 35

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	14.5 mm	Width (inches)	0.571 inch
Height	14.5 mm	Height (inches)	0.571 inch
Depth	8 mm	Depth (inches)	0.315 inch
Net weight	1.3 g	Diameter	14.5 mm

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

Material data

Material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

Additional technical data

Installation advice	Direct mounting
---------------------	-----------------

Dimensions

Diameter	14.5 mm
----------	---------

Classifications

ETIM 5.0	EC002641	ETIM 6.0	EC002848
UNSPSC	30-21-18-01	eClass 6.2	27-26-07-08
eClass 7.1	27-44-03-12	eClass 8.1	27-44-03-12
eClass 9.0	27-14-11-92	eClass 9.1	27-14-11-92

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Engineering Data	STEP