

**IE-PP-V01P**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



For protecting your devices against dust and dirt.

**General ordering data**

Type	IE-PP-V01P
Order No.	<a href="#">1965690000</a>
Version	Plug housing protective cap
GTIN (EAN)	4032248653911
Qty.	10 pc(s).

**IE-PP-V01P**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Net weight 11 g

**Temperatures**

Operating temperature, max. 70 °C      Operating temperature, min. -40 °C  
 Operating temperature -40 °C...70 °C

**General data**

Colour black      Housing main material PA 6 GF  
 Protection degree IP67      Type of mounting Indoors only

**Classifications**

ETIM 3.0	EC001121	ETIM 4.0	EC000437
ETIM 5.0	EC000437	ETIM 6.0	EC002040
UNSPSC	30-21-18-17	eClass 5.1	27-26-12-03
eClass 6.2	27-26-12-03	eClass 7.1	27-44-02-02
eClass 8.1	27-44-02-02	eClass 9.0	27-37-12-07
eClass 9.1	27-44-02-90		

**Approvals**

Approvals



ROHS Conform

**Downloads**

Approval/Certificate/Document of Conformity [UL Approval](#)  
[GOST Approval](#)  
 Brochure/Catalogue [CAT 9 IETH 15/16 EN](#)  
[FL FIELDWIRING EN](#)  
[PI PROFINET CABLING EN](#)  
 User Documentation [MAN IE GUIDE DE](#)  
[MAN IE GUIDE EN](#)