

IE-BP-V01P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



For protecting your devices against dust and dirt.

General ordering data

Type	IE-BP-V01P
Order No.	1965700000
Version	Flange-mounted housing, protective cap
GTIN (EAN)	4032248653928
Qty.	10 pc(s).

IE-BP-V01P**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 12.2 g

Temperatures

Operating temperature, max.	70 °C	Operating temperature, min.	-40 °C
Operating temperature	-40 °C...70 °C		

General data

Colour	black	Housing main material	PA 6 GF
Protection degree	IP67	Type of mounting	Indoors only

Standards

Certificate no. (cULus) E316369

Classifications

ETIM 3.0	EC001121	ETIM 4.0	EC000437
ETIM 5.0	EC000437	ETIM 6.0	EC002040
UNSPSC	30-21-18-17	eClass 5.1	27-26-12-03
eClass 6.2	27-26-12-03	eClass 7.1	27-44-02-02
eClass 8.1	27-44-02-02	eClass 9.0	27-37-12-07
eClass 9.1	27-44-02-90		

Approvals

Approvals



ROHS Conform

Downloads

Approval/Certificate/Document of Conformity	UL Approval GOST Approval
Brochure/Catalogue	CAT 9 IETH 15/16 EN FL FIELDWIRING EN PI PROFINET CABLING EN
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN