

**LaserMark
LM MT300 105/105 SI****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Similar to illustration



- Adhesive polyester labels
- Suitable for A4 laser printers
- Abrasion-resistant
- High heat resistance
- For marking all kinds of switchgear and modules
- Can also be written on with a ballpoint pen or STI marking pen

General ordering data

Type	LM MT300 105/105 SI
Order No.	1975160000
Version	LaserMark, Device markers, 105 x 105 mm, silver
GTIN (EAN)	4032248672264
Qty.	10 pc(s).

LaserMark LM MT300 105/105 SI

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	105 mm	Width (inches)	4.134 inch
Height	105 mm	Height (inches)	4.134 inch
Depth	0.08 mm	Depth (inches)	0.003 inch
Net weight	10.1 g		

General data

Adhesive	Acrylate adhesive	Approval acc. to UL 969	Yes
Colour	silver	Halogen	No
Material	Polyester, PVC-free	Number of markers per packaging unit	40
Number per sheet	4	Operating temperature range	-40...150 °C
Printing method	Laser print	UL 94 flammability rating	HB
Version	Self-adhesive	Width	105 mm

Classifications

ETIM 3.0	EC001288	ETIM 4.0	EC001288
ETIM 5.0	EC001288	ETIM 6.0	EC001288
UNSPSC	30-21-18-01	eClass 5.1	27-14-91-29
eClass 6.2	27-14-91-29	eClass 7.1	27-14-91-29
eClass 8.1	27-14-91-03	eClass 9.0	27-40-06-29
eClass 9.1	27-40-06-29		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Engineering Data	STEP
Product Change Notification	PCN CableLine_DE PCN CableLine_EN
Software	M-Print PRO configuration file

**LaserMark
LM MT300 105/105 SI**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

