

B KOTR M12 5P A BU SAI**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Depending on the choice of cover, there are many circuit board connectors to choose from. The M12 PCB connectors are available as A-coded, B-coded and also D-coded versions. It should be noted that the EA cover and the I/O cover of the 54 mm enclosures require different M12 connectors.

General ordering data

| | |
|------------|----------------------------|
| Type | B KOTR M12 5P A BU SAI |
| Order No. | 2326170000 |
| GTIN (EAN) | 4032248594092 |
| Qty. | 360 pc(s). |

B KOTR M12 5P A BU SAI**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 4.053 g

Technical specifications, empty housing

| | | | |
|------------------|------------------|-----------------------|---------------------------------------|
| Cable glands | M 12 | Coding | A |
| Contact material | Gold-plated | Housing main material | LCP |
| No. of poles | 5 | Protection degree | IP67, when fully mounted |
| Rated current | 4 A | Rated voltage | 30 V |
| Shielded | No | Type of connection | Solder connection (reflow-compatible) |
| Version | Socket connector | | |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 6.0 | EC000438 | eClass 6.2 | 27-06-90-90 |
| eClass 7.1 | 27-06-90-90 | eClass 8.1 | 27-06-90-90 |
| eClass 9.1 | 27-44-02-05 | | |

Approvals

ROHS Conform

DownloadsBrochure/Catalogue [CAT 8 SAI 15/16 EN](#)
[FL FIELDWIRING EN](#)