

**SAI-SK-M12-UNI 2029****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Protective caps protect unassigned plug-in stations against external influences.

**General ordering data**

Type	SAI-SK-M12-UNI 2029
Order No.	<a href="#">2330260000</a>
Version	Protected component assemblies, Protective cap
GTIN (EAN)	4032248592067
Qty.	20 pc(s).

## SAI-SK-M12-UNI 2029

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	1.35 g
------------	--------

## Temperatures

Ambient temperature	-25 °C...+70 °C
---------------------	-----------------

## General data

Cable glands	M 12	Housing main material	PA 66
Material	PA 66	Protection degree	IP67
Temperature range of housing	-20 ... +90 °C		

## Classifications

ETIM 4.0	EC002556	ETIM 5.0	EC002556
ETIM 6.0	EC002314	UNSPSC	30-21-18-01
eClass 6.2	27-06-92-90	eClass 7.1	27-06-92-90
eClass 8.1	27-06-92-90	eClass 9.0	27-44-02-92
eClass 9.1	27-44-02-08		

## Approvals

Approvals



ROHS	Conform
------	---------

## Downloads

Brochure/Catalogue	<a href="#">CAT U_REMOTE 16/17 EN</a> <a href="#">CAT 9 IETH 15/16 EN</a> <a href="#">CAT 8 SAI 15/16 EN</a> <a href="#">FL FIELDWIRING EN</a>
--------------------	---