

B KOTR M12 4P D BU SAI**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Depending on the choice of cover, there are many circuit board connectors to choose from. The M12 PCB connectors are available as A-coded, B-coded and also D-coded versions. It should be noted that the EA cover and the I/O cover of the 54 mm enclosures require different M12 connectors.

General ordering data

Type	B KOTR M12 4P D BU SAI
Order No.	2341480000
GTIN (EAN)	4032248668724
Qty.	360 pc(s).

B KOTR M12 4P D BU SAI**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 3.747 g

Technical specifications, empty housing

Cable glands	M 12	Coding	D
Contact material	Gold-plated	Housing main material	LCP
No. of poles	4	Protection degree	IP67, when fully mounted
Rated current	4 A	Rated voltage	30 V
Shielded	No	Type of connection	Solder connection (reflow-compatible)
Version	Socket connector		

Classifications

ETIM 6.0	EC000438	eClass 6.2	27-06-90-90
eClass 7.1	27-06-90-90	eClass 8.1	27-06-90-90
eClass 9.1	27-44-02-05		

Approvals

ROHS Conform

DownloadsBrochure/Catalogue [CAT 8 SAI 15/16 EN](#)
[FL FIELDWIRING EN](#)