

**SAK Series
TW RSF3 PA**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image

Similar to illustration

Klippon® Connect with clamping yoke Technology

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Type	TW RSF3 PA
Order No.	3877960000
Version	SAK Series, Separation plate, 1.5 mm, beige, Direct mounting
GTIN (EAN)	4008190132323
Qty.	10 pc(s).

SAK Series
TW RSF3 PA

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Width	1.5 mm	Width (inches)	0.059 inch
Height	58 mm	Height (inches)	2.283 inch
Depth	51.5 mm	Depth (inches)	2.028 inch
Net weight	4.85 g		

Temperatures

Storage temperature, max.	40 °C	Storage temperature, min.	10 °C
Storage temperature	10 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

Material data

Material	Polyamide 66	Colour	beige
UL 94 flammability rating	V-2		

System specifications

Version	Intermediate plate
---------	--------------------

Additional technical data

Installation advice	Direct mounting	Snap-on	Yes
---------------------	-----------------	---------	-----

Classifications

ETIM 3.0	EC000886	ETIM 4.0	EC000886
ETIM 5.0	EC000886	ETIM 6.0	EC000886
UNSPSC	30-21-18-27	eClass 5.1	27-14-11-33
eClass 6.2	27-14-11-33	eClass 7.1	27-14-11-33
eClass 8.1	27-14-11-33	eClass 9.0	27-14-11-92
eClass 9.1	27-14-11-33		

Approvals

ROHS	Conform
------	---------