

**OMNIMATE Housing - TERMINALBOX
KOPL DK5 PA**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Open miniature housing in modular terminal format with five screw connections. Potentiometer and status displays can be routed upwards. A cover plate for closing off the housing is also available.

General ordering data

Type	KOPL DK5 PA
Order No.	4036790000
Version	Electronics housings, Head, Accessories
GTIN (EAN)	4008190455323
Qty.	500 pc(s).

**OMNIMATE Housing - TERMINALBOX
KOPL DK5 PA**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Length	77 mm	Length (inches)	3.031 inch
Width	6 mm	Width (inches)	0.236 inch
Height	61 mm	Height (inches)	2.402 inch
Net weight	0.184 g		

System characteristics

Version	Head	Protection degree	IP20
---------	------	-------------------	------

Material data

Colour	beige	Colour chart (similar)	RAL 1001
UL 94 flammability rating	V-2	Storage temperature, min.	-25 °C
Storage temperature, max.	55 °C	Max. relative humidity during storage	80 %
Operating temperature, min.	-50 °C	Operating temperature, max.	100 °C
Temperature range, installation, min.	-25 °C	Temperature range, installation, max.	100 °C

Classifications

ETIM 3.0	EC001284	ETIM 5.0	EC002848
UNSPSC	30-21-18-01	eClass 6.2	27-14-92-14
eClass 7.1	27-14-92-14	eClass 8.1	27-14-92-14

Notes

Notes

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	FL ANALO.SIGN.CONV. EN MB DEVICE MANUF. EN FL MACHINE SAFETY EN FL 72H SAMPLE SER EN PO OMNIMATE EN
--------------------	---