

RKDG D11 PT6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Extensive range of accessories for the FieldPower® boxes.

Cable seals, plug-in connectors, locking elements and much more.

General ordering data

Type	RKDG D11 PT6
Order No.	4323210000
Version	FieldPower®, round, IP65, 9 mm - 11 mm
GTIN (EAN)	4032248641215
Qty.	10 pc(s).

RKDG D11 PT6

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Net weight 4.22 g

Temperatures

Operating temperature

Storage temperature

General data

Clamping range, max.	11 mm	Clamping range, min.	9 mm
Colour	black	Halogen	No
Line type	round	Material	EPDM
Protection degree	IP65	Silicone-free	Yes
Thickness	18 mm	UL 94 flammability rating	HB

Classifications

ETIM 3.0	EC000879	ETIM 4.0	EC000879
ETIM 5.0	EC000879	ETIM 6.0	EC002498
UNSPSC	31-18-16-02	eClass 5.1	23-07-00-00
eClass 6.2	23-07-90-90	eClass 7.1	23-07-90-90
eClass 8.1	23-07-90-90	eClass 9.0	27-14-11-92
eClass 9.1	27-14-25-90		

Approvals

ROHS Conform

Downloads

Approval/Certificate/Document of Conformity	FieldPower
Engineering Data	EPLAN
Engineering Data	STEP