

**RKDG D15 PT6****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Extensive range of accessories for the FieldPower® boxes.

Cable seals, plug-in connectors, locking elements and much more.

**General ordering data**

Type	RKDG D15 PT6
Order No.	<a href="#">4323220000</a>
Version	FieldPower®, round, IP65, 13 mm - 15 mm
GTIN (EAN)	4032248641222
Qty.	10 pc(s).

**RKDG D15 PT6****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight	3.45 g
------------	--------

**Temperatures**

Operating temperature

Storage temperature

**General data**

Clamping range, max.	15 mm	Clamping range, min.	13 mm
Colour	black	Halogen	No
Line type	round	Material	EPDM
Protection degree	IP65	Silicone-free	Yes
Thickness	18 mm	UL 94 flammability rating	HB

**Classifications**

ETIM 3.0	EC000879	ETIM 4.0	EC000879
ETIM 5.0	EC000879	ETIM 6.0	EC002498
UNSPSC	31-18-16-02	eClass 5.1	23-07-00-00
eClass 6.2	23-07-90-90	eClass 7.1	23-07-90-90
eClass 8.1	23-07-90-90	eClass 9.0	27-14-11-92
eClass 9.1	27-14-25-90		

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">FieldPower</a>
Engineering Data	<a href="#">EPLAN</a>
Engineering Data	<a href="#">STEP</a>