

RKDG D13 PT6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Extensive range of accessories for the FieldPower® boxes.

Cable seals, plug-in connectors, locking elements and much more.

General ordering data

| | |
|------------|---|
| Type | RKDG D13 PT6 |
| Order No. | 4323230000 |
| Version | FieldPower®, round, IP65, 11 mm - 13 mm |
| GTIN (EAN) | 4032248641239 |
| Qty. | 10 pc(s). |

RKDG D13 PT6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

| | |
|------------|--------|
| Net weight | 2.36 g |
|------------|--------|

Temperatures

Operating temperature

Storage temperature

General data

| | | | |
|----------------------|-------|---------------------------|-------|
| Clamping range, max. | 13 mm | Clamping range, min. | 11 mm |
| Colour | black | Halogen | No |
| Line type | round | Material | EPDM |
| Protection degree | IP65 | Silicone-free | Yes |
| Thickness | 18 mm | UL 94 flammability rating | HB |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC000879 | ETIM 4.0 | EC000879 |
| ETIM 5.0 | EC000879 | ETIM 6.0 | EC002498 |
| UNSPSC | 31-18-16-02 | eClass 5.1 | 23-07-00-00 |
| eClass 6.2 | 23-07-90-90 | eClass 7.1 | 23-07-90-90 |
| eClass 8.1 | 23-07-90-90 | eClass 9.0 | 27-14-11-92 |
| eClass 9.1 | 27-14-25-90 | | |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|---|----------------------------|
| Approval/Certificate/Document of Conformity | FieldPower |
| Engineering Data | EPLAN |
| Engineering Data | STEP |