

Accessories

CB 135/2.5 NATUR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



CB cable ties for the fastening of cables and markers.

- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
- IEC 62275: 2006-conformant
- Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

General ordering data

Type	CB 135/2.5 NATUR
Order No.	7940006040
Version	Cable ties, Height x width: 135 x 2.5 mm, Polyamide 66, 80 N
GTIN (EAN)	4032248520107
Qty.	100 pc(s).

Data sheet

**Accessories
CB 135/2.5 NATUR**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	2.5 mm	Width (inches)	0.098 inch
Height	135 mm	Height (inches)	5.315 inch
Depth	1 mm	Depth (inches)	0.039 inch
Net weight	0.38 g		

Installation materials

Cable diameter, max.	32 mm	Material	Polyamide 66
Operating temperature range, max.	85 °C	Operating temperature range, min.	-40 °C
Tensile strength	80 N	UL 94 flammability rating	V-2

Classifications

ETIM 3.0	EC000046	ETIM 4.0	EC000046
ETIM 5.0	EC000046	ETIM 6.0	EC000046
UNSPSC	30-21-18-01	eClass 5.1	27-14-07-02
eClass 6.2	27-14-07-02	eClass 7.1	27-14-07-02
eClass 8.1	27-14-07-02	eClass 9.0	27-14-07-02
eClass 9.1	27-14-07-02		

Approvals

Approvals



ROHS Conform

Downloads

Approval/Certificate/Document of Conformity [DE PI830000 160627 001](#)
 Engineering Data [EPLAN, WSCAD](#)

Data sheet

Accessories
CB 135/2.5 NATUR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

