

**RIDERSERIES RCL
SRC CLIP LP**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image

Weidmüller RIDERSERIES relays guarantee a noise-free, decoupled signal transmission in industrial automation concepts.

The are compact, quickly installed and can be fitted in the tightest of spaces.

- 1 NO contact,
- 1 or 2 CO contacts
- optionally with 1 or 2 hard gold plated CO contacts
- optionally: AC or DC coils
- pluggable LED modules with protective functions
- Plastic retaining clip
- Base with screw / tension-clamp connection

General ordering data

Type	SRC CLIP LP
Order No.	8691090000
Version	RIDERSERIES RCL, Retaining clip
GTIN (EAN)	4032248361793
Qty.	10 pc(s).

Data sheet

**RIDERSERIES RCL
SRC CLIP LP**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Net weight 1.97 g

Temperatures

Humidity	40 °C / 93 % rel. humidity, no condensation	Operating temperature, max.	70 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C	Operating temperature	-40 °C...70 °C
Storage temperature	-40 °C...85 °C		

General data

Version	for low relays	Material	Plastic
Colour	black		

Insulation coordination

Protection degree IP20

Classifications

ETIM 4.0	EC001456	ETIM 5.0	EC002586
ETIM 6.0	EC002586	UNSPSC	30-21-19-17
eClass 5.1	27-37-16-03	eClass 6.2	27-37-16-03
eClass 7.1	27-37-92-08	eClass 8.1	27-37-92-08
eClass 9.1	27-37-16-92		

Approvals

Approvals



ROHS Conform

Downloads

Engineering Data [EPLAN, WSCAD](#)

Data sheet

**RIDERSERIES RCL
SRC CLIP LP**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Dimensional drawing

