

**RIDERSERIES RCI  
SRC CLIP HM**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Product image**


Clip-on RS 30. 31. 32 relay bases are available in widths from 11.2 to 25 mm, depending on the type.

The RSM relay multiplexers are available as 4, 8 and 16-way modules. To reduce the wiring work, the DC variants are fitted with a common plus or minus potential. The optional IEC603-1 plug-in connector enables the connection of pre-assembled lines.

The screw connection system is used to connect the conductor with a rated cross-section of 2.5 mm<sup>2</sup>.

**General ordering data**

Type	SRC CLIP HM
Order No.	<a href="#">8692620000</a>
Version	RIDERSERIES RCI, Retaining clip
GTIN (EAN)	4032248364169
Qty.	100 pc(s).

**Data sheet**

**RIDERSERIES RCI  
SRC CLIP HM**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Net weight 0.42 g

**Temperatures**

Humidity 40 °C / 93 % rel. humidity, no condensation      Operating temperature

Storage temperature

**General data**

Version for high relays      Material metal  
 Colour silver

**Insulation coordination**

Protection degree IP20

**Classifications**

ETIM 4.0	EC001456	ETIM 5.0	EC002586
ETIM 6.0	EC002586	UNSPSC	30-21-19-17
eClass 5.1	27-37-16-03	eClass 6.2	27-37-16-03
eClass 7.1	27-37-92-08	eClass 8.1	27-37-92-08
eClass 9.1	27-37-16-92		

**Approvals**

Approvals



ROHS Conform

**Downloads**

Engineering Data [EPLAN, WSCAD](#)