

**RIDERSERIES RCM
SCM-I CLIP P**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image



Plastic retaining clip for RIDERSERIES RCM relays

General ordering data

Type	SCM-I CLIP P
Order No.	8869440000
Version	RIDERSERIES RCM, Retaining clip
GTIN (EAN)	4032248614295
Qty.	10 pc(s).

Data sheet

**RIDERSERIES RCM
SCM-I CLIP P**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	27 mm	Width (inches)	1.063 inch
Height	37.8 mm	Height (inches)	1.488 inch
Depth	54.2 mm	Depth (inches)	2.134 inch
Net weight	4.744 g		

Temperatures

Humidity	40 °C / 93 % rel. humidity, no condensation	Operating temperature, max.	70 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C	Operating temperature	-40 °C...70 °C
Storage temperature	-40 °C...85 °C		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

General data

Material	Plastic	Colour	orange
----------	---------	--------	--------

Classifications

ETIM 4.0	EC001456	ETIM 5.0	EC002586
ETIM 6.0	EC002586	UNSPSC	30-21-19-17
eClass 5.1	27-37-16-03	eClass 6.2	27-37-16-03
eClass 7.1	27-37-92-08	eClass 8.1	27-37-92-08
eClass 9.1	27-37-16-92		

Approvals

Approvals	
ROHS	Conform

Downloads

Brochure/Catalogue	CAT 4.2 ELECTR 18/19 EN
Engineering Data	EPLAN.WSCAD
Engineering Data	STEP

Data sheet

**RIDERSERIES RCM
SCM-I CLIP P**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Dimensional drawing

