

**RIDERSERIES RCM  
SCM-I CLIP N**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Product image**

Plastic retaining clip for RIDERSERIES RCM relays

**General ordering data**

Type	SCM-I CLIP N
Order No.	<a href="#">8875620000</a>
Version	RIDERSERIES RCM, Retaining clip
GTIN (EAN)	4032248608577
Qty.	10 pc(s).

**Data sheet**

**RIDERSERIES RCM  
SCM-I CLIP N**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Width	27 mm	Width (inches)	1.063 inch
Height	24 mm	Height (inches)	0.945 inch
Depth	55.5 mm	Depth (inches)	2.185 inch
Net weight	3.74 g		

**Temperatures**

Humidity	40 °C / 93 % rel. humidity, no condensation	Operating temperature, max.	70 °C
Operating temperature, min.	-40 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C	Operating temperature	-40 °C...70 °C
Storage temperature	-40 °C...85 °C		

**Environmental Product Compliance**

REACH SVHC                      Lead 7439-92-1

**General data**

Version	for low screw connection base	Material	Plastic
Colour	orange		

**Classifications**

ETIM 4.0	EC001456	ETIM 5.0	EC002586
ETIM 6.0	EC002586	UNSPSC	30-21-19-17
eClass 5.1	27-37-16-03	eClass 6.2	27-37-16-03
eClass 7.1	27-37-92-08	eClass 8.1	27-37-92-08
eClass 9.1	27-37-16-92		

**Approvals**

Approvals



ROHS                                      Conform

**Downloads**

Brochure/Catalogue	<a href="#">CAT 4.2 ELECTR 18/19 EN</a>
Engineering Data	<a href="#">EPLAN_WSCAD</a>
Engineering Data	<a href="#">STEP</a>

**Data sheet**

**RIDERSERIES RCM  
SCM-I CLIP N**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Dimensional drawing**

