

Connecting elements
H1,5/18**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

For conductors from 0.25 to 6,0 mm² (AWG 24 - 10)

tin-plated copper

dimensional tolerances to DIN 46228 part 1

- supplied loose in polybag

General ordering data

Type	H1,5/18
Order No.	9004070000
Version	Wire-end ferrule, uninsulated, 18 mm
GTIN (EAN)	4008190105761
Qty.	1,000 pc(s).
Packaging	loose

Connecting elements

H1,5/18

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	18 mm	Width (inches)	0.709 inch
Net weight	0.15 g		

Technical data

Version	uninsulated
---------	-------------

Wire-end ferrules

Collar diameter (D2)	2.8 mm	Conductor cross-section	1.5 mm ²
Contact surface diameter (D1)	1.7 mm	L1 in mm	18 mm
Stripping length	18 mm	Wire connection cross section AWG, max.	AWG 16

Classifications

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000005	ETIM 6.0	EC000005
UNSPSC	31-16-31-02	eClass 5.1	27-40-02-01
eClass 6.2	27-40-02-01	eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01	eClass 9.0	27-40-02-01
eClass 9.1	27-40-02-01		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP

Connecting elements H1,5/18

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Similar to illustration

