

## Connecting elements H10,0/24,0X R SV

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



- In multi-pack bag
- Weidmüller colour code

### General ordering data

Type	H10,0/24,0X R SV
Order No.	<a href="#">9006830000</a>
Version	Wire-end ferrule, insulated, 17 mm, 12 mm, red
GTIN (EAN)	4008190332310
Qty.	100 pc(s).
Packaging	Multipack bag

**Data sheet**

**Connecting elements  
H10,0/24,0X R SV**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**

**Dimensions and weights**

Width	24 mm	Width (inches)	0.945 inch
Net weight	0.64 g		

**Technical data**

Version	insulated
---------	-----------

**Wire-end ferrules**

Collar diameter (D2)	9.6 mm	Colour code	Weidmüller
Conductor cross-section	10 mm <sup>2</sup>	Contact surface diameter (D1)	4.6 mm
Contact surface length (L2)	12 mm	L1 in mm	24 mm
Metal sleeve thickness (S1)	0.2 mm	Plastic collar thickness (S2)	0.3 mm
Stripping length	17 mm	Wire connection cross section AWG, max.	AWG 8

**Classifications**

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000005	ETIM 6.0	EC000005
UNSPSC	31-16-31-02	eClass 5.1	27-40-02-01
eClass 6.2	27-40-02-01	eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01	eClass 9.0	27-40-02-01
eClass 9.1	27-40-02-01		

**Approvals**

Approvals



ROHS Conform

**Downloads**

Brochure/Catalogue	<a href="#">CAT 6 TOOLS 15/16 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>
Engineering Data	<a href="#">STEP</a>

**Data sheet**

**Connecting elements  
H10,0/24,0X R SV**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Similar to illustration**

---

