

## Connecting elements H10/30S ZH EB

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

### General ordering data

|            |  |
|------------|--|
| Type       | H10/30S ZH EB  |
| Order No.  | <a href="#">9018870000</a>                                   |
| Version    | Wire-end ferrule, Twin wire-end ferrule, 23 mm, 18 mm, Ivory |
| GTIN (EAN) | 4032248105823  |
| Qty.       | 100 pc(s).   |
| Packaging  | loose  |

## Connecting elements H10/30S ZH EB

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

|            |        |                |            |
|------------|--------|----------------|------------|
| Width      | 30 mm  | Width (inches) | 1.181 inch |
| Net weight | 1.07 g |                |            |

### Technical data

|         |                       |
|---------|-----------------------|
| Version | Twin wire-end ferrule |
|---------|-----------------------|

### Wire-end ferrules

|   |            |                             |                    |
|---|------------|-----------------------------|--------------------|
| Collar height (A)                       | 13.4 mm    | Collar width (B)            | 7.6 mm             |
| Colour code                             | Weidmüller | Conductor cross-section     | 10 mm <sup>2</sup> |
| Contact surface diameter (D1)           | 6.5 mm     | Contact surface length (L2) | 18 mm              |
| L1 in mm                                | 30 mm      | Metal sleeve thickness (S1) | 0.2 mm             |
| Plastic collar thickness (S2)           | 0.5 mm     | Stripping length            | 23 mm              |
| Wire connection cross section AWG, max. | AWG 8      |                             |                    |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC000005    | ETIM 4.0   | EC000005    |
| ETIM 5.0   | EC000005    | ETIM 6.0   | EC000005    |
| UNSPSC     | 31-16-31-02 | eClass 5.1 | 27-40-02-01 |
| eClass 6.2 | 27-40-02-01 | eClass 7.1 | 27-40-02-01 |
| eClass 8.1 | 27-40-02-01 | eClass 9.0 | 27-40-02-01 |
| eClass 9.1 | 27-40-02-01 |            |             |

### Approvals

Approvals



|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                    |                                      |
|--------------------|--------------------------------------|
| Brochure/Catalogue | <a href="#">CAT 6 TOOLS 15/16 EN</a> |
| Engineering Data   | <a href="#">WSCAD, EPLAN</a>         |
| Engineering Data   | <a href="#">STEP</a>                 |

**Data sheet**

**Connecting elements  
H10/30S ZH EB**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Similar to illustration**

---

