


Connecting elements H0,75/16D GR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



- supplied loose in polybag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Type	H0,75/16D GR
Order No.	9019050000
Version	Wire-end ferrule, insulated, 12 mm, 10 mm, grey
GTIN (EAN)	4008190033002
Qty.	500 pc(s).
Packaging	loose

Connecting elements

H0,75/16D GR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	16 mm	Width (inches)	0.63 inch
Net weight	0.09 g		

Technical data

Version	insulated
---------	-----------

Wire-end ferrules

Collar diameter (D2)	2.8 mm	Colour code	DIN
Conductor cross-section	0.75 mm ²	Contact surface diameter (D1)	1.2 mm
Contact surface length (L2)	10 mm	L1 in mm	16 mm
Metal sleeve thickness (S1)	0.15 mm	Military designation	T 20A 006 A
Plastic collar thickness (S2)	0.25 mm	Stripping length	12 mm
Wire connection cross section AWG, max.	AWG 18		

Classifications

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000005	ETIM 6.0	EC000005
UNSPSC	31-16-31-02	eClass 5.1	27-40-02-01
eClass 6.2	27-40-02-01	eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01	eClass 9.0	27-40-02-01
eClass 9.1	27-40-02-01		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP

Connecting elements H0,75/16D GR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Drawings

Similar to illustration

