

Connecting elements
H6,0/26D GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Type	H6,0/26D GE
Order No.	9019230000
Version	Wire-end ferrule, insulated, 20 mm, 18 mm, yellow
GTIN (EAN)	4008190072117
Qty.	100 pc(s).
Packaging	loose

Connecting elements

H6,0/26D GE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	26 mm	Width (inches)	1.024 inch
Net weight	0.5 g		

Technical data

Version	insulated
---------	-----------

Wire-end ferrules

Collar diameter (D2)	6.3 mm	Colour code	DIN
Conductor cross-section	6 mm ²	Contact surface diameter (D1)	3.5 mm
Contact surface length (L2)	18 mm	L1 in mm	26 mm
Metal sleeve thickness (S1)	0.2 mm	Military designation	T 20A 023 A
Plastic collar thickness (S2)	0.3 mm	Stripping length	20 mm
Wire connection cross section AWG, max.	AWG 10		

Classifications

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000005	ETIM 6.0	EC000005
UNSPSC	31-16-31-02	eClass 5.1	27-40-02-01
eClass 6.2	27-40-02-01	eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01	eClass 9.0	27-40-02-01
eClass 9.1	27-40-02-01		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP