

Connecting elements
H16,0/28D BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

Type	H16,0/28D BL
Order No.	9019270000
Version	Wire-end ferrule, insulated, 21 mm, 18 mm, blue
GTIN (EAN)	4008190100773
Qty.	100 pc(s).
Packaging	loose

Connecting elements

H16,0/28D BL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	28 mm	Width (inches)	1.102 inch
Net weight	0.83 g		

Technical data

Version	insulated
---------	-----------

Wire-end ferrules

Collar diameter (D2)	8.8 mm	Colour code	DIN
Conductor cross-section	16 mm ²	Contact surface diameter (D1)	5.8 mm
Contact surface length (L2)	18 mm	L1 in mm	28 mm
Metal sleeve thickness (S1)	0.2 mm	Military designation	T 20A 027 A
Plastic collar thickness (S2)	0.4 mm	Stripping length	21 mm
Wire connection cross section AWG, max.	AWG 6		

Classifications

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000005	ETIM 6.0	EC000005
UNSPSC	31-16-31-02	eClass 5.1	27-40-02-01
eClass 6.2	27-40-02-01	eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01	eClass 9.0	27-40-02-01
eClass 9.1	27-40-02-01		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP