

Connecting elements
H35,0/39D R**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

General ordering data

Type	H35,0/39D R
Order No.	9019330000
Version	Wire-end ferrule, insulated, 28 mm, 25 mm, red
GTIN (EAN)	4008190048365
Qty.	50 pc(s).
Packaging	loose

Connecting elements

H35,0/39D R

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	39 mm	Width (inches)	1.535 inch
Net weight	1.74 g		

Technical data

Version	insulated
---------	-----------

Wire-end ferrules

Collar diameter (D2)	12.7 mm	Colour code	DIN
Conductor cross-section	35 mm ²	Contact surface diameter (D1)	8.3 mm
Contact surface length (L2)	25 mm	L1 in mm	39 mm
Metal sleeve thickness (S1)	0.2 mm	Military designation	T 20A 033 A
Plastic collar thickness (S2)	0.4 mm	Stripping length	28 mm
Wire connection cross section AWG, max.	AWG 2		

Classifications

ETIM 3.0	EC000005	ETIM 4.0	EC000005
ETIM 5.0	EC000005	ETIM 6.0	EC000005
UNSPSC	31-16-31-02	eClass 5.1	27-40-02-01
eClass 6.2	27-40-02-01	eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01	eClass 9.0	27-40-02-01
eClass 9.1	27-40-02-01		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Engineering Data	STEP